

Geocel® ecoSEAL PAINTERS MATE

FLEXIBLE ACRYLIC FILLER

Geocel® ecoSEAL Painters Mate Flexible Acrylic Filler is a highly flexible acrylic sealant for use on internal and external surfaces including skirting boards, door and window frames, floorboards, ceilings, walls and plasterboard. Resists cracking, no sanding is required and can be overpainted approximately 1 hour after application

- High performance acrylic
- For internal and external use
- Can be overpainted in 1 hour
- No sanding required
- Available in White, 300ml sausages, box quantity 12, 12 nozzles per box

SPECIFICATIONS

Manufactured under ISO 9001



TECHNICAL DATA

Storage Life 24 months stored in original containers

between 4°C and 25°C

White Colour **Skin Time** 30 - 45 minutes

Specification writers: These values are not intended for use in preparing specifications. Please contact your local Geocel® Sales Representative prior to writing specifications on this product.

APPLICATION

To be applied using a Geocel® ecoSEAL Sleeve and a Cox Powerflow CARTRIDGE Heavy Duty Skeleton Gun. Surfaces to be sealed should be clean and dry. Smooth surface within 5 minutes.

Sealant application between +5°C to +30°C. Store in dry conditions above 4°C.

PACKAGING

Geocel® ecoSEAL Painters Mate Flexible Acrylic Filler is supplied in 300ml sausages packed in boxes of 12.

ANCILLARY MATERIALS & EQUIPMENT

Powerflow CARTRIDGE Cox

Geocel® ecoSEAL Sleeve

Geocel® ecoSEAL Spare Nozzles

Geocel® ecoSEAL Spare Lid

HEALTH AND SAFETY

Health and Safety data sheets available on request.

TECHNICAL SERVICE

For further technical information, advice on suitability for specific applications, or detailed Health and information, contact Geocel® Technical Safety Service.

IMPORTANT NOTE The information contained herein is offered in good faith and is believed to be accurate. However, because conditions and methods of use of our products are beyond our control, this information should not be used in substitution for customer's tests to ensure that Geocel's products are safe, effective and fully satisfactory for the intended end use. Suggestions of use shall not be taken as inducements to infringe any patent.

Geocel's sole warranty is that the product will meet the Geocel sales specifications in effect at the time of shipment

Your exclusive remedy for breach of such warranty is limited to refund of purchase price or replacement of any product shown to be other than as warranted

Geocel specifically disclaims any other express or implied warranty of fitness for a particular purpose or merchantability

Geocel disclaims liability for any incidental or consequential damage





Geocel