

FEATURES

- 5 meter white LED strip light
- 60 LEDs per metre
- Wide viewing angle of 120°
- IP65 waterproof rating for protection against dust and water jets from all angles
- Available in a variety of colours
- Voltage rating of 12
- RoHS (Restriction of Hazardous Substances) compliant

RS PRO White LED Strip 5m 12V

RS Stock No.: 883-7894



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

LED Strip Lights



Product Description

RS PRO white LED strip lights are a simple lighting solution for any interior or exterior setting. These LED lights come with a self-adhesive backing, so they're simple to install. Versatile and quick to fix, they can be cut to size, adapted to contours and bent around corners and curves. These LED light strips are set in crystal resin for IP65 waterproof protection. They're also dust-tight and defended against water jets from any angle, making them popular in bathrooms or under kitchen units.

General Specifications

LED Colour(s)	White
Number of LEDs per Metre	60
Flexible/Rigid	Flexible

Colour Specification

Colour	Colour Temperature	Typical Luminous Flux (lm/m)
Cool White	5500K - 7000K	550lm/m
White	4000K - 4500K	450lm/m
Warm White	2700K - 3200K	400lm/m

Electrical Specifications

Voltage Rating	12V
Current Rating	400mA (per metre)
Power Per Metre	4.8W



Mechanical Specifications

Strip Length	5m
Strip Width	10mm
Beam Angle	120°

Protection Category

Approvals

Compliance/Certifications RoHS



