



ENGLISH

## Datasheet

# SNYD Series Insulated Crimp Ring Terminal 12 → 10 AWG, M3, Blue Nylon

RS Stock number [267-3795](#)



### Specifications:

#### MAXIMUM ELECTRIC CURRENT :

A.W.G.	22	20	18	16	14
AMP.	9	12	17	18	30

**MAXIMUM ELECTRICAL RATING:** 105°C 600 VOLTS MAX.

**INSULATION MATERIAL :** NYLON

#### INSULATION COLOR :

22-16 A.W.G.: RED  16-14 A.W.G.: BLUE

**DOUBLE CRIMP :** WITH COPPER SLEEVE ON BARREL

**TERMINAL MATERIAL :** COPPER