




# Shockwave HSS-G TiN Red Hex 2 mm - 2 pcs

## RED HEX - SHOCKWAVE™ HSS-TiN METAL DRILL BITS

- Impact rated drill bit with 1/4" hex shank optimised for impact drivers.
- Titanium Nitride coating dispenses heat and makes the drill bit suitable for use also in high speed.
- QUAD EDGE™ Tip: unique combination of 135° split point and four cutting edges: 135° split point allows for precise & fast drilling start without walking. Four cutting edges create smaller chips to prevent heat build up for longer life.
- Variable flute geometry: For faster material ejection. Helps the bit run cooler and prevent it from burning out faster.
- Enhanced tapered web: Wider core towards the shank of the drill bit. Strengthens the core to increase overall flute durability.



|                     |          |
|---------------------|----------|
| ø (mm)              | 2        |
| Article Number      | 48894703 |
| Pack quantity       | 2        |
| Total length (mm)   | 59.5     |
| Working length (mm) | 17       |