


06130040

RCK 13 - Self centring

2D Technical Drawing

Dynamic 3D View
Technical Specifications

Part number (CODE)	06130040
Ød (DD) mm	40
ØD (D) mm	65
L1 (L1) mm	17
L2 (L2) mm	22
L3 (L3) mm	28
L (L) mm	34
Maximum torque Mt (MT) Nm	1200
Clamping pressure - Shaft (CPS) N/mm ²	235
Clamping pressure - Hub (CPH) N/mm ²	145
Clamping screws DIN 912 MAT. 12.9 - Num. (CSN)	8
Clamping screws DIN 912 MAT. 12.9 - Type (CST)	M6x20
Clamping screws DIN 912 MAT. 12.9 - Torque (CSTQ) Nm	14
Extraction thread - Type (ETT)	M6
Extraction thread - Num. (ETN)	4
Weight (WEIGHT) kg	0.40