

FEATURES

- Flat head hexagonal socket screws to DIN7991 standards
- A2 stainless steel
- Generally non-magnetic
- Cannot be hardened by heat treatment
- Supplied in a polypropylene case

410 piece Stainless Steel Screw/Bolt Kit, M3, M4, M5, M6

RS Stock No.: 393-179



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

From the trusted RS PRO brand comes this set of high-quality flat head hexagonal socket screws. Socket screws have a cylindrical head and an internal hex drive and are tightened using an Allen or Hex key, making them ideal for use in applications where externally wrenched fasteners are not practical because of a lack of space. Flat-headed socket screws provide a more flush finish with the material as there is no extrusion past the surface of the screw head.

General Specifications

| | |
|-------------------------|--|
| Number Of Pieces | 410 |
| Screw/Bolt Type | Socket Screw |
| Head Shape | Flat |
| Drive Type | Hex Socket |
| Kit Contents | M3 x 10 Quantity- 50 M3 x 12 Quantity- 50 M4 x 10 Quantity- 50 M4 x 12 Quantity- 50 M4 x 16 Quantity- 50 M5 x 12 Quantity- 30 M5 x 16 Quantity- 30 M5 x 20 Quantity- 20 M5 x 25 Quantity- 20 M6 x 12 Quantity- 30 M6 x 16 Quantity- 20 M6 x 30 Quantity- 10 |
| Applications | Carpentry, Construction and roofing, DIY applications |

Mechanical Specifications

| | |
|-----------------------------------|-----------------|
| Screw/Bolts Lengths | 10mm to 30mm |
| Thread Size | M3, M4, M5, M6 |
| Material | Stainless Steel |
| Stainless Steel Type | A2 304 |
| Finish | Plain |
| Screw/Bolt Length Longest | 30mm |
| Screw/Bolt Length Shortest | 10mm |
| Specification | DIN7991 |



| Kit Contents | | | |
|--------------|----------|---------|----------|
| Size | Quantity | Size | Quantity |
| M3 x 10 | 50 | M5 x 16 | 30 |
| M3 x 12 | 50 | M5 x 20 | 20 |
| M4 x 10 | 50 | M5 x 25 | 20 |
| M4 x 12 | 50 | M6 x 12 | 30 |
| M4 x 16 | 50 | M6 x 16 | 20 |
| M5 x 12 | 30 | M6 x 30 | 10 |

393-179



| | | | |
|-----------------------|-----------------------|-----------------------|-----------------------|
| M6 x 16 RS 171-893 | M6 x 12 RS 171-887 | M6 x 30 RS 171-922 | M5 x 12 RS 171-843 |
| M5 x 16 RS 171-859 | M4 x 16 RS 171-837 | M5 x 25 RS 171-871 | M5 x 20 RS 171-865 |
| M4 x 10 RS 171-815 | M3 x 10 RS 171-792 | M3 x 12 RS 171-809 | M4 x 12 RS 171-821 |