



Sample photo

Order symbol: P 081106
Product nbr: 7094150
Description: Enclosure
Remarks: Polyester

EAN: 6418074004345
El. number:
 Finland 3423656
 Denmark 8212005617
 Italy 7331015
 Sweden 2536207

Including: Base, cover with EPDM gasket and stainless steel cover screws.

Dimensions:			L		W		H		Rating:		
mm:	75	110	55					Ingress Protection (EN 60529): IP 66/67			
inch:	3	4.3	2.2					Impact Resistance (EN 50102): IK 08			
Materials:										Electrical insulation: Totally insulated	
Material:	GRP								Halogen free (DIN/VDE 0472, Part 815): Yes		
Base colour:	RAL 7001								UV resistance: UL 508		
Cover colour:	RAL 7001								Flammability Rating (UL 746 C 5): UL 94 5V		
Cover screws material:	Stainless steel								Glow Wire Test (IEC 695-2-1) °C: 960		
Gasket material:	EPDM								NEMA Class: NEMA 1, 4, 4X, 12, 13		
Temperatures:										Certificates:	
Short term:	-50 ... 120 °C										
Continuous:	-40 ... 80 °C										
Short term:	-60 ... 250 °F										
Continuous:	-40 ... 175 °F										
Accessories:											
PM 0811	Mounting plate										
PRM 0811	DIN-15 Mounting rail										
MRS 28540	Wall fastening lug set										

