

CUAL EK 281913 G 50mm²



Sample image

Order symbol : CUAL EK 281913 G 50mm²

Product nr : 2674640

Description : Terminal enclosure

EAN : 6418074319692

El. number :

- Finland : 3424738
- Denmark : 8212052877
- Sweden : 2674640

Dimensions :	Height	Width	Depth
mm :	280	190	130
inch :	11.02	7.48	5.12

Materials :

Material :	Polycarbonate
Base colour :	RAL_7035
Cover colour :	RAL 7035 -light grey
Gasket material :	Polyurethane

Temperatures :

Temperature °C (continuous) :	-40 ... 80
Temperature °F (continuous) :	-40 ... 175

Ratings :

Ingress protection (EN 60529):	IP66; IP67;
Impact Resistance (EN 62262):	IK08;
electrical_insulation :	Totally insulated
Halogen free (DIN/VDE 0472, Part 815) :	Yes
UV resistance :	UL 746C
Flammability Rating :	UL 94 V0
Glow Wire Test (IEC 695-2-1) °C :	960C