




Peli lights - Water resistant - LED technology heads ups



A hybrid LED/Xenon hands-free light. The 2620 gives you the option of using the Xenon lamp for intense bright light or 3 LEDs to conserve battery life. The multi-angle pivoting head allows you to aim light where you need it. A rubber strap for hard hat use and adjustable cloth strap for bare head use are both included. The HeadsUp Lite 2620 is perfect for hiking, camping, or for any task that require both hands. Powered by 3 AAA alkaline cells (included). Certified to ATEX Zone 2 (Category 3).



Materials

Peli lights - Water resistant - LED technology heads ups

ANSI FL1 Specifications

	High	Low
LIGHT SOURCE.	Incandescent (Xenon)	
BATTERIES	3 AAA Alkaline (Included)	
CHARGE TIME	N/A	
VOLTAGE	4.5	
LENGTH	5.5 cm (2.16")	
WEIGHT W/ BATTERIES	0.13 kg (4.5 oz.)	
WEIGHT W/O BATTERIES	0.1 kg (3.5 oz.)	

Body	Lens	Shroud	Switch Type
ABS Resin	Polycarbonate Resin	ABS Resin	Push button Lo/Hi On/Off switch
Clip	Contact, Spring & Retainer	O-Ring	Night Vision Film
	Stainless Steel and Brass Nickel Plate	Ethylene Propylene	

Configuration

Cat. #	Description
--------	-------------

Peli lights - Water resistant - LED technology heads ups Accessories

Cat. #	Description
2624	HeadsUp Lite 2620 Lamp

FL1 STANDARD	High	Low
LIGHT OUTPUT 		9.00 LUMENS
RUNTIME (hours/min) 	2h 15m	80 hrs.
BEAM DISTANCE (meters) 	44m	29 m.
PEAK BEAM INTENSITY (candela) 	491cd	216cd

Approvals

CE Ex - II 3 G EEx nL IIC T3X
Certificate: TRL Report# XU1006/4804

ETL us - Class I, Div. 1, GP C,D, T3C CONFORMS TO
STD. UL 783