



LOC	DIST	REVISIONS					
G	14	P	LTR	DESCRIPTION	DATE	DWN	APVD
			H	REV PER ECR 10-000722	22JAN10	JR	TM



AMP WIRE RANGE	Listed FILE E13288	LR7189 Certified
2/0 AWG SOLID OR STRANDED	2/0 AWG STRANDED	2/0 AWG SOLID OR STRANDED

- 1 STAMP AMP 2/OW* APPROX AS SHOWN
- 2 TIN PLATE 0.00254 [.000100] MIN THK PER ASTM B-545
- 3 BRIGHT TIN LEAD PLATE 0.00254 [.000100] MIN EXT THK PER B-545
- 4 COPPER PER ASTM B-152, ANNEALED
- 5 MEETS MS20659-136, CLASS 2



50	LOOSE PIECE	3	2-321873-2
50	LOOSE PIECE	2	321873
QTY	PACKAGE TYPE	FINISH	PART NO.

MAX RECOMMENDED OPERATING TEMPERATURE: 170°C MAX	THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DK SCHRUM 1/14/94	Tyco Electronics Corporation Harrisburg, PA 17105-3608			
	DIMENSIONS: MM [INCHES]		CHK AJ KAUFMAN 1/19/94				
VOLTAGE RATING: N/A			APVD JL MECKLEY 1/19/94	NAME TERMINAL, RING TONGUE, SOLISTRAND			
CIRCULAR MIL AREA: 60.6-76.3mm² [119,500-150,500] SOLID OR STRANDED			PRODUCT SPEC —	SIZE A2			
	MATERIAL - 4		APPLICATION SPEC —	CAGE CODE 00779			
			WEIGHT —	DRAWING NO 321873			
			CUSTOMER DRAWING	RESTRICTED TO —			
			SEE TABLE	SCALE 2:1			
				SHEET 1 of 1			
				REV H			