

Product information

Job Site Radio DAB



DMR109

Battery Type	Lithium-ion
Body only machine	1
Battery Range	7.2 - 18 v
Speakers	2x76mmØ (8Ω)
Practical Output (7.2v)	0.5W x 2
Practical Output (10.8v)	1.2W x 2
Practical Output (14.4v)	2.2W x 2
Practical Output (18v)	3.5W x 2
Frequency Range DAB	Band III 5A – 13F
FM Coverage	87.5 - 108 Mhz
Net weight	4.6 kg



STANDARD EQUIPMENT: AC power adaptor

- Newly compatible with 10.8V CXT slide batteries
- Dual power source: AC or Makita batteries.
- Digital tuner
- Flexible antenna can be removed and stored inside the radio.
- Soft grip carry handle swivels 90 degrees
- 2 speaker stereo system.
- Elastomer bumpers protect against rough handling on a jobsite
- Equipped with Micro USB port for software upgrade.
- AUX-IN jack for connecting to external audio source (Connecting cable is not included.)
- AC adaptor jack
- IP64 rated dust and shower-proof construction
- Easy-to-read digital tuner with LCD display

Details correct as of: 4-5-2017

Makita reserve the right to change specifications at any time owing to their policy of constant improvement.

Accessories shown are not necessarily supplied.

www.makitauk.com