

## D 19 L 17

### Socket 1/2"

Bi-hexagon UD profile, long pattern

Code	ETIM
<b>6140330</b>	<b>EC002203</b>
EAN	UNSPSC
<b>4010886614037</b>	<b>27-11-17-04</b>
Country of origin	eCl@ss
<b>Germany</b>	<b>21-04-02-19</b>
Customs tariff number	
<b>82042000</b>	



### Article description

- Acc. to DIN 3124, ISO 2725-1
- Square drive as per DIN 3120 - C 12,5, ISO 1174, with ball retention groove
- Manually operated, with non-slip cross knurling
- chrome vanadium steel, ground, chrome-plated
- Sizes 16, 18, 21 mm with hole drilled for tommy bar Ø 8 mm

### Article information

Contents (Qty of pieces)	1	Standard	DIN 3124 DIN 3120 - C 12,5 ISO 1174
Net weight [kg]	0,133 kg	Width across flats 1 [mm]	17
Total length [mm]	77 mm	Backup	Ball Catching Cricket
Total width [mm]	24 mm	Insert-Ø 1	24,0 mm
Surface	polished, chrome-plated	Working length	77,0 mm
Material	Chrome-vanadium steel	Insert-Ø 2	24,0 mm
Drive connector square female (metric)	12,5 mm	Operating depth	16,5 mm
Drive connector square female [inch]	1/2"		