



PRODUCT-DETAILS**SS16/25M****16MM GS CONDUIT 25M - MET**

General Information

Extended Product Type:	SS16/25M
Product ID:	7TCA296120R0014
EAN:	5020963007224
Catalog Description:	16MM GS CONDUIT 25M - MET
Long Description:	Inherent Low Fire Hazard Conduit, Nominal Conduit Size 16mm, Outside Diameter 16.0mm, Inside Diameter 13.0mm, Static Bend Radius 35mm, Reel Length 25 Meters, 316 Stainless Steel, Corrosion Resistant
Display Name:	SS16/25M

Additional Information

Product Main Type:	Adaptaflex Flexible Cable Protection
Application:	Indoors / Outdoors - Corrosive Environments

Ordering

EAN:	5020963007224
-------------	---------------

UPC: 786210249544

Dimensions

Outside Diameter: 16.0 mm

Technical

Number of Batteries: 0

Material: Stainless Steel

Environmental

WEEE Category: Product Not in WEEE Scope

RoHS Information: Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019

Container Information

Package Level 1 Units: 1 piece

Package Level 1 EAN: 5020963007224

Package Level 1 Height: 6 in
152 mm

Package Level 1 Depth / Length: 13 in
330 mm

Package Level 1 Width: 13 in
330 mm

Certificates and Declarations

Declaration of Conformity - CE: 9AKK107492A9618

RoHS Declaration: 9AKK107992A8994

REACH Declaration: 9AKK107992A8994

External Classifications and Standards

ETIM 8: EC001179 - Protective metallic hose

ETIM 9: EC001179 - Protective metallic hose

UNSPSC: 39131706

Categories

Products > Low Voltage Products and Systems > Installation Products > Cable Protection, Explosion Proof and Lighting > Flexible Cable Protection Systems

