



Main

| | |
|---------------------------|-------------|
| Range of product | Odace |
| Aesthetic name | Styl |
| Product or component type | Cover frame |
| Number of gangs | 1 gang |
| Type of frame | Single |
| Type of packing | Flow-pack |


Complementary

| | |
|-------------------------------|---|
| Device mounting | Flush |
| Fixing mode | Clip-in |
| Colour tint | Aluminium |
| Surface finish | Matt |
| Surface treatment | Painted |
| Material | Thermoplastic ABS-UV stabilised: decorative frame |
| Height | 85 mm |
| Width | 85 mm |
| Depth | 10 mm |
| Net weight | 0.01264 kg |
| Resistance to chemical agents | Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid Resistant to diluted quaternary ammonium Resistant to diluted bleach Resistant to diluted ammonia Resistant to soapy water Resistant to crystal cleaner Resistant to hydrogen peroxide 10 volumes Resistant to hexane |

Environment

| | |
|---------------------------------------|--|
| Ambient air temperature for storage | -5...50 °C |
| Ambient air temperature for operation | 5...45 °C |
| Standards | 2006/95/EEC UNE 20315-1-1 EN 60669-1 NF C 61-314 |
| Product certifications | AENOR: 030/2205[RETURN]LCIE: NF 603415A[RETURN]N[RETURN]NF |
| IK degree of protection | IK04 |
| IP degree of protection | IP21D |

Offer Sustainability

| | |
|----------------------------|--|
| Sustainable offer status | Green Premium product |
| Cradle to Cradle |  Bronze |
| REACH Regulation |  REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| Sustainable packaging | Yes |
| RoHS exemption information |  Yes |
| China RoHS Regulation |  China RoHS Declaration |
| Environmental Disclosure |  Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |