



ENGLISH

Datasheet
Stock No. 791-8276

Halogen Lamp



Specifications

220v-240vac, 50hz
With J-118" Erp/C" Class Max 400w China Bulb
Tempered Glass Shade
Product Size: 18.5x14.5x18.2cm
Epoxy matt black finish
GS/EMC/IP44 Certificated

Feature

No need for ballast or ignitor circuits
Die-cast aluminium body
Hinged toughened glass lens sealed with a silicone rubber gasket
Dimpled anodised aluminium reflector provides a wide spread of light
Halogen bulb supplied
Robust, practical and weather proof, IP44 rated halogen floodlight with wall mounting bracket
Halogen Lamps are small, lightweight