

## Han Q 8/0-HBM Metal



Image is for illustration purposes only. Please refer to product description.

Part number	09 12 008 0301
Specification	Han Q 8/0-HBM Metal
HARTING eCatalogue	<a href="https://harting.com/09120080301">https://harting.com/09120080301</a>

### Identification

Category	Hoods / Housings
Series of hoods/housings	Han-Compact®
Type of hood/housing	Bulkhead mounted housing

### Version

Size	Han-Compact®
Locking type	Single locking lever
Field of application	Hoods/housings for industrial applications

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	12

### Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Chromated
Colour (hood/housing)	RAL 9005 (jet black)
Material (seal)	NBR
Material (locking)	Stainless steel
RoHS	not compliant
ELV status	not compliant



**Pushing Performance**  
Since 1945

## Material properties

China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

## Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076
	UL 2237 PVVA2.E318390
	CSA-C22.2 No. 182.3 ECBT8.E235076
	CSA-C22.2 No. 182.3 PVVA8.E318390
Approvals	CE DNV GL

## Commercial data

Packaging size	10
Net weight	53.333 g
Country of origin	Romania
European customs tariff number	85389099
GTIN	5713140017542
eCl@ss	27440202 Shell for industrial connectors
ETIM	EC000437
UNSPSC 24.0	39121466