

Main

Range	New Unica
Device application	Mounting
Product or component type	Cover frame
Aesthetic name	Unica Pro
Number of gangs	1 gang
Installation direction	Horizontal
Type of frame	Single
Number of modules	10 modules
Fixing mode	Clip-in
Colour tint	Anthracite (RAL 7021)

Complementary

Material	Thermoplastic ABS-UV stabilised: cover frame Polycarbonate: intermediate plate
Standards	IEC 60884-1 IEC 60669-1
Width	298 mm
Height	85 mm
Depth	10 mm
Net weight	0.046 kg
Resistance to chemical agents	Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid Resistant to diluted quaternary ammonium Resistant to diluted bleach Resistant to diluted ammonia Resistant to soapy water Resistant to crystal cleaner Resistant to hydrogen peroxide 10 volumes Resistant to hexane

Environment

IK degree of protection	IK04
IP degree of protection	IP21D

Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
Sustainable packaging	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations