

Datasheet

ENGLISH

RS PRO, DC Motor Controller, Voltage Control, 6 - 15 V dc, 3 A, Panel Mount

Stock No: 417-9728



Specifications:

Supply Voltage	6 – 15 v
Current Rating	3 A
Voltage Rating	6 – 15 V dc
Compatible Motor Type	Brushed DC Motor
Mounting Style	Panel Mounted
Length	62mm
Width	41mm
Depth	25mm
Weight	32g

NOTE:

The products optimum performance is at 12v dc. Using lower voltages, although useful, will alter the products performance and consistency in operation. Supply and output cables must be trimmed to 21cm to meet current EMC regulations.

Edge to edge frequency, min 1136 Hz, max 1250 Hz, average 1200 Hz. Mark to space varies motor speed.