



Product data sheet

Power tools for trade & industry

Optical Level

PRO GOL 20 D



Robust and reliable – ideal for outdoor use

The most important data

| | |
|-----------------|-----------------|
| Unit of measure | 360 degrees |
| Magnification | 20 x |
| Accuracy | ± 3.0 mm at 30m |

Order number 0 601 068 402

Technical data

Additional data

| | |
|----------------------------|-----------------|
| Dust and splash protection | IP 54 |
| Unit of measure | 360 degrees |
| Magnification | 20 x |
| Accuracy | ± 3.0 mm at 30m |
| Working range | 60 m |
| Operating temperature | -10 – 50 °C |
| Storage temperature | -20 – 70 °C |
| Weight, approx. | 1.5 kg |
| Working range, value | 60 m |



Product data sheet

Power tools for trade & industry

Advantages:

- Ideal for outdoor use due to a robust housing with dust and splash protection (IP54)
- Fast aperture for excellent staff reading
- Compensator lock for safe transport



You can find more information about the deviations in the following link: <https://www.bosch-professional.com/eg/en/wac/>

