



MCB 2P 10kA C-16A 2M

NCN216A

Technical Properties

Type of pole	2 P
Curve	C
Rated short circuit breaking capacity	10 kA
Rated current	16
Rated operational AC voltage	230/400
Number of poles	2 P
type of connection	with screw
Top and bottom screw terminals connection capacity with flexible cable	1 to 25 mm ²
Top and bottom screw terminals connection capacity with rigid cable	1 to 35 mm ²
Number of modules	2
Rated short circuit breaking capacity 400V 50Hz	10 kA
Tightening torque	2,8Nm
European directive RoHs	voluntary compliance
European directive WEEE	not concerned