

Datasheet

**RS Pro Stainless Steel Adjustable Height Mount 98mm
Rubber 115mm 45mm 158mm 1000kg 120mm M12 3.5°
RS Stock No: 688-256**



Product Details

RS Pro stainless steel adjustable height mount is designed for use in applications that impose strict safety and reliability demands on the installation and damping of light and medium duty machinery. The stainless steel machine mount is designed to meet the specific requirements imposed in humid, wet or corrosive environments within the process industry or in environments where there are important hygiene requirements such as in the food, drinks and pharmaceuticals industries. The built in levelling bolt means the stainless steel mounts can be adjusted within a large range with considerable accuracy, allowing a 7° inclination while still maintaining stability.

Features and Benefits

- Withstands light to medium loads
- Articulated bolt for inclined surfaces
- 1000 kg static load capacity
- Rubber foot



ENGLISH

Specifications:

Base Material	Stainless Steel
Diameter	98 mm
Foot Material	Rubber
Maximum Adjustment Height	115 mm
Minimum Adjustment Height	45 mm
Overall Height	158 mm
Static Load Capacity	1000 kg
Thread Length	120 mm
Thread Size	M12
Tilt Angle	3.5°