

För icke direkt toleranssatta mått gäller toleransklass  
General tolerances if not otherwise stated

NOM DIM MM		TOL CLASS		
From	To	A	B	C
(1)	6	±0.05	±0.1	±0.2
(6)	30	±0.1	±0.2	±0.5
(30)	100	±0.15	±0.3	±0.8
(100)	300	±0.2	±0.5	±1.2
(300)	1000	±0.3	±0.8	±2

Hål / Holes H13

Skarpa kanter brutna där ej annat anges.  
No sharp edges unless otherwise specified.

Övriga generella toleranser enligt ritning 4100-4644.  
Additional general tolerances in accordance with drawing 4100-4644.




Rev	Change order	Change: A = Added W = Was D = Deleted	Date	Sign
6	P2716	4100-3851 W 4101-3332 456-7709 W RS 456-7709	091102	SE

LASERMÄRKNING/LASER MARKING:

FONT: GEN-ISO

Datumkod / Date code "YYYYYY"

Serienummer / Serial number "XXXXXXX"



- 4101-2610
- 4100-3776
- 4101-2383 - placering position B
- 4101-2614

Packas enligt förpackningsritning 4101-2725  
Packed according to drawing 4101-2725

Material		Behandling/Treatment			Status	
Konstr./Design TGW	Ritad/Drawn TGW	Datum/Date 2009-11-02	Skala/Scale 1:1	Kontr./Checked MAHA	Godk./Approved NE	Frisläppt
Benämning/Denomination KRIMPTÅNG RS Flag Terminals CRIMPING TOOL 456-7709				Vikt/Weight,gram 43002882		Art grp 012
				Ritn nr/Drawing no 43002882		REV 006