

60 CP 10

Single open ended spanner

adjustable, chromed

Code	ETIM
6381100	EC002192
EAN	UNSPSC
4010886638118	27-11-17-26
Country of origin	eCl@ss
China	21-04-01-01
Customs tariff number	
82041200	



Article description

- Acc. to ISO 6787
- Jaw set at 15°
- Swedish pattern, roller with left hand thread
- With adjusting scale
- Chromium vanadium steel
- Chrome-plated, polished heads
- Chrome-plated, pin gun-metal finish
- With hanging hole

Article information

Contents (Qty of pieces)	1	Graduation	0-30
Version/Execution	Swedish pattern, roller with left hand thread	Total length [inch]	10
Net weight [kg]	0,42 kg	Jaw set	15 °
Total length [mm]	252 mm	Ratchet function	no
Total width [mm]	66 mm	Clamping width [mm]	30 mm
Total height [mm]	15 mm	Clamping width [inch]	1.3/16
Surface	chrome plated, heads polished, pin burnished	Width across flats 1 [AF]	-
Material	Chrome-vanadium steel	Suspension hole	yes
Standard	ISO 6787	Setting scale	yes