

Features

- Threaded Silencer
- Brass
- Maximum Input Pressure 12 Bar
- Minimum Operating Temperature -10°C
- Maximum Operating Temperature +80°C
- Filtration Treshold 100 µm

RS PRO Pneumatic Silencers

RS Stock No.: 0631958



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

This range of RS PRO Pneumatic Silencers, designed for use with compressed air, pneumatics, and industrial water circuit applications. This high-quality fitting ensures optimum performance for operations that use high pressure and high temperature, without compromising the longevity of the fitting. The pneumatic fitting allows easy connection and installation with other components, saving on valuable time and resource.

General Specifications

Type	Threaded Silencer	
Material	Brass, Bronze	
Body Material	Brass	
Inlet Connection Type	Threaded	
Threaded Inlet Connection Gender	Male	
Threaded Inlet Connection	G 1/4 Male	
Threaded Inlet Connection Thread Size	1/4 in	
Maximum Input Pressure	12 Bar	
Minimum Operating Pressure	-10°C	
Maximum Operating Pressure	+80°C	
Filtration Threshold	100 µm	
Noise Reduction	72 dBa*	*Noise level in (dB) at 6 bar

Dimensions

A	F	H	CH	dB*
1/4	7	18	16	72

