



## POLIFAN flap disc PFC 125x22.23 mm conical Z40 Uni. Line PSF STEELOX steel/stainless steel (10)

**POLIFAN flap disc PFC 125x22.23 mm conical Z40 Uni. Line PSF STEELOX steel/stainless steel (10)**

Item number: [67764125](#)

EAN: [4007220377345](#)

The entry-level range Universal Line PSF includes robust tools for processing the most common materials. Universal Line PSF tools achieve good results with high economic efficiency.

POLIFAN flap disc for steel and stainless steel (INOX) with aggressive stock removal rate and good tool life.

### Technical information

|                 |                    |
|-----------------|--------------------|
| Abrasive        | Zirconia alumina Z |
| Dia. external   | 125 mm             |
| Dia. hole       | 22.23 mm           |
| Grit size       | 40                 |
| Max. RPM        | 12200 RPM          |
| Mounting system | Centre hole        |
| Shape           | PFC / B / T29      |
| Version         | No information     |

### Advantages

- ✓ Fast work progress and high economic efficiency thanks to the good stock removal rate.
- ✓ Good tool life.
- ✓ Also suitable for low-power angle grinders.

## Materials that can be worked

- ✓ Stainless steel (INOX)
- ✓ Steel

---

## Applications

- ✓ Chamfering
- ✓ Deburring
- ✓ Step-by-step fine grinding
- ✓ Surface grinding
- ✓ Work on weld seams

---

## Drive types

- ✓ Angle grinder
  - ✓ Cordless angle grinder
  - ✓ Drive spindle
- 



August Rüggeberg GmbH & Co. KG  
Hauptstraße 13  
51709 Marienheide

+49 2264 9-0

+49 2264 9-400

[info@pferd.com](mailto:info@pferd.com)