

6850 // 3D CUT F

Cut protection gloves
PPE risk category II



The thinnest cut protection gloves with performance level F
21 Gauge
Touchscreen capable



6850 // 3D CUT F



Material:	Special yarn, navy blue
Coating:	Nitrile micro foam, black
Size(s):	7-12
Packaging unit:	100 pair(s)
Certification:	EN 388, OEKO-TEX STANDARD 100®

NITRAS 3D CUT F, cut protection gloves, special yarn (polyester / HPPE / tungsten / elastane), navy blue, nitrile micro foam coating, black (colour code: 2110), partly coated on palm and fingertips, high mechanical resistance, knitted wrist, highest cut resistance (performance level F), perfect dexterity, perfect and innovative fit thanks 3D FIT, unique comfort and protection for the user, 21 Gauge, reinforced thumb crotch, touchscreen capable, premium quality, for food contact, OEKO-TEX STANDARD 100®, ANSI A6 CUT, very slip resistant, perfect grip, very high abrasion resistance, very good dry and oil grip, PPE risk category II

EN 388

EN ISO 21420



4X41F

21
GAUGE



Size	6	7	8	9	10	11	12
Colour coding system							

Industries

- Craft
- Building / Construction
- Automotive manufacturing
- Commissioning / shipping
- Wood processing

Advantages

- + The thinnest cut protection gloves with performance level F
- + 21 Gauge
- + Touchscreen capable



Performance values

EN 388:2016 + A1:2018	Test parameter	Performance levels	Test result
 4X41F	Abrasion resistance	1-4	4
	Blade cut resistance (Coupe-Test)	1-5	X
	Tear resistance	1-4	4
	Puncture resistance	1-4	1
	Blade cut resistance (TDM)	A-F	F
EN ISO 21420:2020	Test parameter	Performance levels	Test result
	Dexterity	1-5	5

Additional information

	Material	Colour
Palm	Nitrile micro foam on special yarn	black
Index finger and thumb	Nitrile micro foam on special yarn	black
Back of the hand	Special yarn	navy blue
Fingertips	Nitrile micro foam on special yarn	black
Cuff / knitted wrist	Special yarn	navy blue

Logistics data

Size	GTIN (SPU)	GTIN (PU)	Length (m)	Width (m)	Height (m)	Weight (kg)	Quantity PU / pallet
6	4059904216884	4059904216952	0,56 m	0,3 m	0,28 m	4,59 kg	42
7	4059904216891	4059904216969	0,56 m	0,3 m	0,28 m	4,99 kg	42
8	4059904216907	4059904216976	0,56 m	0,3 m	0,28 m	5,39 kg	42
9	4059904216914	4059904216983	0,56 m	0,3 m	0,28 m	5,79 kg	42
10	4059904216921	4059904216990	0,56 m	0,3 m	0,28 m	6,29 kg	42
11	4059904216938	4059904217003	0,56 m	0,3 m	0,28 m	6,79 kg	42
12	4059904216945	4059904217010	0,56 m	0,3 m	0,28 m	7,29 kg	42

Customs tariff number: 61161020910

Country of origin: China