

Product sheet Miniature connectors


 Product
 Female cable connector, cable outlet 3-6 mm
 Pole
 12

 Area
 M16 connectors IP 40
 serie 680
 Article number
 09 0330 00 12


illustration




scale drawing



Item description



Contact Arrangement



	X	Υ
Α	-0,41	-3,45
В	2,29	-3,61
C	4,10	-1,21
D	3,20	1,34
E	2,71	3,59
F	0,41	3,45
G	-2,29	3,61
Н	-4,10	1,21
J	-3,20	-1,34
K	-2,71	-3,59
L	2,00	-1,51
M	-2,00	1,51

Technical data

Common values

Female cable connector Connector Design Screw-locking Connector locking system solder Termination 0,25 mm² Wire gauge (mm) 24 Wire gauge (AWG) 3 - 6 mm Max. Cable outlet +85 °C Upper temperature -40 °C Lower temperature

Electrical values

60 V Rated voltage 500 V Rated impulse voltage 1 Pollution degree Overvoltage category ı Ш Material group 3 A Rated current (40°C) ≤ 3 mΩ Volume resistivity not shielded EMV compliance IP 40 Degree of protection >500 mating cycles Mechanical operation

Material

Material of contact CuSn (bronce)
Contact plating Au (gold)
Material of contact body PBT (UL 94 V-0)
Material of housing PA (UL 94 HB)

Cable data

Contacts 12, female cable connector, cable outlet 3 - 6 mm, gold plated contacts

