

Datasheet

## RS Pro 32A Yellow 2P+E Pole Plastic Industrial Socket, 100 to 130 V, IP67

RS Stock No: **760-9042**



### Product Details

RS Pro industrial socket in yellow colour, has 2P+E poles. It is suitable for industrial applications that require a current of up to 32 A and a voltage ranging from 100 to 130 V. This panel mount device has plastic construction. The IP67 rated device offers a high level of ingress protection and is well suited for dusty or damp environments.

### Features and Benefits

- Flip-up cap
- Panel mount
- IP67 rated

**Specifications:**

Colour	Yellow
Current Rating	32 A
Depth	68 mm
Dimensions (W x H x D)	75 x 75 x 68 mm
Height	75 mm
International Protection Rating	IP67
Material	Plastic
Minimum Box Depth	42 mm
Mounting Style	Panel Mount
Number of Poles	2P+E
Number of Sockets	1
Number of Ways	3
RCD Type	None
Voltage Rating	100 to 130 V
Voltage Rating	100 to 130 V
Width	75 mm
Frequency Rating	50/60 Hz
Standards Met	ENEC 03, CE