



verso maintenance trolley with 6 drawers / cupboard & multiplex top. Featuring a robust, fully welded steel housing with double, independent, storage sections, push - pull handles, 100% extension drawers with drawer blocking and 125mm diameter castors. Drawer configuration: 3x 100mm, 2x 125mm, 1x 175mm (50 kg U.D.L.) and cupboard section with single, reinforced, door and 1 galvanised steel shelf (75kg U.D.L.). Finished in durable powder coat paint in RAL 7035 light grey / RAL 3004 crimson red. WxDxH: 1300x600x980mm

Breite [mm]: 1300  
Tiefe [mm]: 600  
Höhe [mm]: 980  
Bruttogewicht [kg]: 130.93  
EAN-Code: 5039350148525  
Zolltarifnummer UK: 94032080  
Ursprungsland: GB

## Produkteigenschaften

|                      |               |
|----------------------|---------------|
| Product surface      | Powder coated |
| Product material     | Sheet steel   |
| Main colour          | Crimson red   |
| Main RAL colour      | RAL 3004      |
| Secondary colour     | Light grey    |
| Secondary RAL colour | RAL 7035      |

## Artikelbeschreibungen

|               |       |
|---------------|-------|
| Product brand | verso |
|---------------|-------|

## Schubladen

|                           |     |
|---------------------------|-----|
| Number of drawers         | 6   |
| Drawer load capacity [kg] | 50  |
| Drawer height 1 [mm]      | 100 |
| Drawer height 2 [mm]      | 100 |

|                      |     |
|----------------------|-----|
| Drawer height 3 [mm] | 100 |
| Drawer height 4 [mm] | 125 |
| Drawer height 5 [mm] | 125 |
| Drawer height 6 [mm] | 175 |

## Schrank, Gehäuse, Werkbank und EAP

|                          |                 |
|--------------------------|-----------------|
| Worktop/housing top type | Beech Multiplex |
| Shelf load capacity [kg] | 75              |
| Door type                | Plain           |
| Door height 1 [mm]       | 725             |