



Damp-Shrink™ KP-HSTTA Heat Shrink

KP-HSTTA

Dual Wall Adhesive Lined Thin Wall Heat Shrink: Plastic Kit Box - Black only.
For DAMP Locations.

Specifications

Product Type	Heat Shrink Tubing
Adhesive Lined	Yes
Color	Black
Material	Cross-Linked Polyolefin
Finish/Coating	Adhesive-Lined
Maximum Operating Temperature (°C)	110
Maximum Operating Temperature (°F)	230
Minimum Operating Temperature (°C)	-55
Minimum Operating Temperature (°F)	-67
Sub Brand	Damp-Shrink™
Overall Length (In.)	6
Overall Length (ft.)	0.5
Overall Length (m)	0.15
Overall Length (mm)	152.4
Standards Met	UL Recognized, MIL SPEC
Shrink Ratio	3:1
Shrink Temperature (°C)	120
Shrink Temperature (°F)	248
Application	3:1 shrink ratio for damp applications. Provides excellent abrasion protection. Flexible

Packaging Detail

UPC	07498370366
Std. Pkg. Qty.	1
Std. Pkg. Volume (cf)	0.0779
Std. Ctn. Qty.	0
Std. Ctn. Volume (cf)	0.0000