

DCH072L2-QW

Perforateur SDS-plus XR 12V 3Ah Li-Ion Brushless 1.1J



5035048741900



Product Description:

Impact force (E.P.T.A.): 1.1J Wood/concrete/metal Push Drill (CPS) 0-4280 Level
temperature (mm): 13/14/10Vibration rate (m/s²): 9.7 of

Product features and benefits:

- Brushless motor for more autonomy and durability Impact force 1.1 J,
- impact rate 0-4280 cps/min, no-load speed 0-910 rpm, ideal for drilling fixing holes in concrete, brick and masonry from 4 mm to 14 mm LED light with timer to illuminate the work area and improve visibility Part of
- the XR 12V platform, A high-performance, easily rechargeable and very compact battery system
-

Product Warranty:

This product has a 1-year warranty extended to 3 years after registration

Included Items:

- Batteries (x2)
- Charger (x1)
- Multi-position side handle (x1)
- Clip ceinture (x1)
- TSTAK Box (x1)

Specifications techniques :

- - ~~Capacity~~
(wood): 13 mm
 - ~~Capacity] Battery:~~
3.0 Ah
 - Weight (including battery): 1.9 Kg
 - - Drilling Capacity (Metal):

10 mm

