

16.4ft (5m) Active High Speed HDMI Cable - Ultra HD 4k x 2k HDMI Cable - HDMI to HDMI M/M

Product ID: HDMM5MA



This Active High Speed HDMI Cable features a built-in active signal booster for a connection distance of up to 15 feet (5m) between your HDMI-enabled devices, with no signal loss. This built-in amplifier circuitry actively boosts the HDMI signal with no external power required.

This high quality HDMI cable fully supports 1080p+ resolutions at up to 120Hz refresh rate, with life-like color. To accommodate the demands of future high definition devices, such as increased resolutions and higher frame rates, this Ultra HD cable supports resolutions up to 4k x 2k.

Please Note: This cable features unidirectional architecture which requires that the cable is installed in the correct direction. Please refer to the "TV" label on the HDMI connector which plugs into your display, in order to ensure that the device and the HDMI source are connected properly.

The terms HDMI, HDMI High-Definition Multimedia Interface, HDMI trade dress and the HDMI Logos are trademarks or registered trademarks of HDMI Licensing Administrator, Inc.

Certifications, Reports and Compatibility



Applications

- Connecting high-definition A/V devices such as Blu-Ray Disc players, HDTVs, DVD Players, DVRs, game consoles, projectors etc., up to 5m away, with no signal loss

Features

- **ACTIVE HIGH SPEED HDMI CABLE:** 16.4 ft (5m) Active High Speed HDMI supports 4K Ultra HD video (3840x2160p, 24, 30Hz), Full HD (1080p 120Hz); HDMI 1.4b
- **ACTIVE CIRCUITRY:** Active bus powered amplifier boosts video signals over longer distances to extend HDMI signal up to 16.4 ft (5m) (no external power supply needed), supports additional color spaces such as Adobe RGB and YCC601 Color
- **DURABLE CABLE:** Ideal for in-wall installations where CL2 rating is required; Flexible PVC jacket; Al-Mylar Foil with Braid shield & gold plated connectors with metal shell improve signal integrity & block external Electromagnetic Interference (EMI)
- **APPLICATIONS:** Use this HDMI cable for home office, conference room, office or classroom; works w/ your laptop/professional workstation/soundbar for presentations via UHD/4K monitors, projectors/large HDTV displays; Samsung/Sony/Apple TV/Dell/Lenovo
- **SPECS:** 16.4 feet (5 meters); Black; HDMI 1.4b; HDMI Cord Male to Male; Jacket: PVC; Shield: Al-Mylar foil w/ Braid; CL2 Fire Rated; ARC, Deep Color, HDCP 1.4, CEC; Note: HDMI connector labelled "TV" connects to the TV/Display side

Hardware

Warranty	2 Years
Connector Plating	Gold
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid
Fire Rating	CL2
Chipset ID	Spectra7 - HT8181

Performance

Maximum Digital Resolutions	3840 x 2160 (Ultra HD 4K) @ 30hz
-----------------------------	----------------------------------

Connector(s)

Connector A	1 - HDMI (19 pin)
Connector B	1 - HDMI (19 pin)

Special Notes / Requirements

Note	This HDMI Cable is unidirectional. Please ensure that the HDMI connector labelled with "TV" is connected to the Display, TV, or Projector.
------	--

Physical

Characteristics

Color	Black
Connector Style	Straight
Wire Gauge	30 AWG
Cable Length	16.4 ft [5 m]
Cable OD	0.2 in [6 mm]
Product Length	16.4 ft [5.0 m]
Product Width	0.7 in [1.9 cm]
Product Height	0.4 in [1.0 cm]
Weight of Product	9.2 oz [261.0 g]

Packaging Information

Package Quantity	1
Package Length	6.4 in [16.3 cm]
Package Width	7.8 in [19.8 cm]
Package Height	1.5 in [3.9 cm]
Shipping (Package) Weight	9.6 oz [272.0 g]

What's in the Box

Included in Package	1 - 5m Active High Speed HDMI Cable - HDMI - M/M
---------------------	--

****Product appearance and specifications are subject to change without notice.***