



61803

Dimensions



d		17	mm
D		26	mm
B		5	mm
d ₁	≈	19.8	mm
D ₁	≈	23.3	mm
r _{1,2}	min.	0.3	mm

Abutment dimensions



d _a	min.	19	mm
D _a	max.	24	mm
r _a	max.	0.3	mm

Calculation data

Basic dynamic load rating	C	2	kN
Basic static load rating	C ₀	1.3	kN
Fatigue load limit	P _u	0.054	kN
Reference speed		56000	r/min
Limiting speed		34000	r/min
Calculation factor	k _r	0.015	
Calculation factor	f ₀	14.1	

Mass

Mass bearing		0.00745	kg
--------------	--	---------	----