



## LENOX Bi-metal Jig Saw Blade – Med Metal

20302BT318S



- Super sharp to cut fast without deflection
- Ground to precision sharpness for straight cuts and a smooth finish
- Designed for optimal performance in cutting medium metal
- Shatter resistant with bi-metal technology

### Description:

The LENOX Bi-metal T-Shank Jig Saw Blade 92mm has been constructed using bi-metal technology which flexes and resists breaking, delivering extended blade life. The ground to precision sharpness of the blade for straight cuts provides a smooth finish. The super sharp blade enables for fast precision cutting without deflection. Ideal for cutting medium metal.

Specifications	
TPI	18
Size	92 x 10 x 0.9 mm
Blade Quantity	2