

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0757345001

Status:

Active

Overview:

SFP+ and SFP Interconnect Solutions

Description:

Small Form-factor Pluggable (SFP) Stacked 2-by-5 Multi-Port Connector with 4 Lightpipes, with Press-fit PC Tails, 200 Circuits, Lead-Free

Documents:

- 3D Model

Application Specification AS-76090-001-001 (PDF)
- Drawing (PDF)

Packaging Specification PK-75733-001-001 (PDF)
- Product Specification PS-75310-001 (PDF)

RoHS Certificate of Compliance (PDF)
- Application Specification AS-75310-001 (PDF)

Agency Certification

CSA

LR19980

UL

E29179

General

Product Family

I/O Connectors

Series

75734

Application

Module-to-Board

Comments

With 4 Lightpipes

Component Type

Receptacle

Overview

SFP+ and SFP Interconnect Solutions

Product Name

SFP

Type

N/A

UPC

822350125963

Physical

Circuits (Loaded)

200

Circuits (maximum)

200

Color - Resin

Black, Clear (Blue Tint)

Durability (mating cycles max)

200

Flammability

94V-0

Lock to Mating Part

Yes

Material - Metal

High Performance Alloy (HPA)

Material - Plating Mating

Gold

Material - Plating Termination

Tin

Material - Resin

High Temperature Thermoplastic, Polycarbonate

Net Weight

125.380/g

Orientation

Right Angle

PC Tail Length

3.05mm

PCB Locator

Yes

PCB Retention

Yes

PCB Thickness - Recommended

2.40mm

Packaging Type

Tray

Panel Mount

No

Pitch - Mating Interface

0.80mm

Plating min - Mating

0.762µm

Plating min - Termination

0.762µm

Polarized to Mating Part

Yes

Polarized to PCB

Yes

Surface Mount Compatible (SMC)

No

Temperature Range - Operating

-40°C to +85°C


Termination Interface: Style

Through Hole - Compliant Pin

Waterproof / Dustproof

No

Electrical



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
-ED/01/2017 (12
January 2017)

Halogen-Free

Status

Low-Halogen

Need more information on product
environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

75734 Series

Use With

75951-0999 SFP Dust Plug

Current - Maximum per Contact	0.5A
Shield Type	EMI Fingers
Shielded	Yes
Voltage - Maximum	30V
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Reference - Drawing Numbers	
Application Specification	AS-75310-001, AS-76090-001-001
Packaging Specification	PK-75733-001-001
Product Specification	PS-75310-001
Sales Drawing	SD-75734-001

This document was generated on 07/26/2017

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION