



PRODUCT-DETAILS

SPUL16/50M
UL-CSA LIST LIQ.TIGHT NC16 50MT GRY



概要信息	
产品型号	SPUL16/50M
产品ID	7TCA296030R0366
欧洲商品编号(EAN)	5020963004551
目录说明	UL-CSA LIST LIQ.TIGHT NC16 50MT GRY
详细描述	Liquid Tight, Medium Flexibility, Covered Steel Conduit, Nominal Conduit Size 16mm, Outside Diameter 17.8mm, Inside Diameter 12.8mm, Static Bend Radius 50mm, Reel Length 50 Meters, UL Listed and CSA Approved, PVC Covered Galvanised Steel Core with Copper Packing, Grey

其他信息	
应用	Flexible Protection Systems
产品应用类型	Liquid Tight, Medium Flexibility Conduit

订货信息	
欧洲商品编号(EAN)	5020963004551
UPC	786210275307

尺寸	
产品净深	50 m

技术参数	
Number of Batteries	0
颜色	Gray
材料	Galvanized Steel Core with PVC Cover and Copper Packing

环境条件	
WEEE 类别	Product Not in WEEE Scope

包装信息	
1级包装单元	1 piece
1级包装高度	9.37 in 238 mm
1级包装长度	19.25 in 489 mm
1级包装宽度	19.25 in 489 mm

认证及声明（文件编码）	
数据手册，技术资料	SPUL16/50M
说明书和手册	SPUL16/50M
符合性声明 - CE	9AKK107492A9618
RoHS信息	9AKK107992A8994
RoHS日期	9AKK107992A8994
REACH Declaration	9AKK107992A8994

分类	
ETIM 8	EC001179 - Protective metallic hose
UNSPSC	39131706

分类

低压产品及系统 → 安装产品 → 电缆保护、防爆和照明 → Flexible Cable Protection Systems

