

Alnico Deep Pot Magnet datasheet

- Alnico 5 magnet material
- Magnetically stable at high temperatures
- Max. operating temperature 220°C
- Mild steel pot
- Brass spacer
- Zinc plated body
- Diameter ground to H6 tolerance
- Custom designs available



Product Information

Product No.	Diameter <i>mm</i>	Height	Weight <i>kg</i>	Pull force	Units / pack
E730	6	10	0.002	0.2	2
E731	8	12	0.004	0.3	2
E732	10	16	0.009	0.5	2
E733	13	18	0.017	1.0	2
E734	16	20	0.029	1.5	2
E735	20	25	0.057	3.5	2
E736	25	30	0.110	8.0	2