

PSD-4; 0...40 bar gauge ; two switching output (PNP/NPN) + 4...20 mA

PSD-4; 0...40 bar gauge ; two switching output (PNP/NPN) + 4...20 mA

Item number: 14240490

Quantity: 1 pcs.

Order code: PSD-4-CZ-BG440-HD1Z-WW-ZZ W1011PS4Z-SZAB-P-GSFI

Overview: PSD-4; 0...40 bar gauge ; two switching output (PNP/NPN) + 4...20 mA
Electronic pressure switch with display
Output signal: two switching output (PNP/NPN) + 4...20 mA
IO-Link: without
Power supply: 15...35 V DC
Measuring range: 0...40 bar gauge
Process connection: G 1/4 A DIN EN ISO 1179-2
Sealing: NBR
Media temperature: -20 ... 85 °C (-4 ... +185 °F)
El. connection: Circular connector M12x1 (5-pin)
pin assignment el. connection: U+=1, U-=3, S+=5, SP1=4, SP2=2
Accuracy: $\pm 0.5\%$ of span
Approvals: cULus
with test protocol
Specifications according to data sheet: PE 81.86

Details: PSD-4; 0...40 bar gauge ; two switching output (PNP/NPN) + 4...20 mA
Electronic pressure switch with display
Output signal: two switching output (PNP/NPN) + 4...20 mA
IO-Link: without
Power supply: 15...35 V DC
Measuring range: 0...40 bar gauge
Process connection: G 1/4 A DIN EN ISO 1179-2
Sealing: NBR
Media temperature: -20 ... 85 °C (-4 ... +185 °F)
El. connection: Circular connector M12x1 (5-pin)
pin assignment el. connection: U+=1, U-=3, S+=5, SP1=4, SP2=2
Accuracy: $\pm 0.5\%$ of span
Approvals: cULus
with test protocol
Specifications according to data sheet: PE 81.86