



ENGLISH

Datasheet

Heat Gun

RS Stock number [778-1860](#)



Description:

Professional hot air gun with set and variable flow for dust free removing of paint and other surface treatments.

Three air flow settings

Ergonomic soft grip handle

Double insulation

Air flow: 350 or 500 l/min

Plastic case, 5 accessories - reduction nozzle, glass protection nozzle, reflector nozzle, flat nozzle, triangular scraper.

Specifications:

Airflow per nozzle:

1) 300 l/min, 2) 300 l/min, 3) 500 l/min

Operating Temperature per nozzle:

1) 50 °C, 2) 70 – 600 °C, 3) 70 - 600 °C

Model Number:

HAG2000

Voltage Rating:

230 V

Wattage:

2000 W

Weight:

0.85 kg