674/C Click-type torque bars, for right-hand and left-hand tightening, in case

UNI EN ISO 6789

Features:
- Round drive Ø 22 mm,
- Torque accuracy: ± 4%,
- Dual scale for accurate torque adjustment
- Safety knob for maintaining set torque value
- When not in use, set torque to lowest value of torque wrench range





	art.	Nm	Kgfm	lbf.ft	Ø mm	L mm	LB mm	LS mm	kg	
006740005	674/C50	100÷500	10÷50	80÷400	22	786	725	56	3,4	1,25
006740008	674/C80	160÷800	16÷80	120÷600	22	997	915	56	4,5	2,0
006740010	674/C100	200÷1000	20÷100	150÷750	22	997	915	56	4,5	2,5



