

Push-in T-fitting QSYLV-1/8-1/4-U

Part number: 153795

FESTO



 General operating condition

Data sheet

Feature	Value
Size	Standard
Nominal size	4.2 mm
Tubing insertion depth	17 mm
Type of seal on screwed plug	Coating
Mounting position	optional
Design	L-shape, dual, parallel
Size of pack	1
Design	Push-pull principle
Operating pressure complete temperature range	-0.095 MPa ... 1 MPa
Operating pressure complete temperature range	-0.95 bar ... 10 bar
Operating pressure complete temperature range	-13.775 psi ... 145 psi
Maritime classification	See certificate
Operating medium	Compressed air to ISO 8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C ... 60 °C
Max. tightening torque	8 Nm
Product weight	25 g
Number of outputs	2
Number of supply lines	1
Type of mounting	Hollow bolt with external hex
Pneumatic connection, port 1	Male thread 1/8 NPT
Pneumatic connection, port 2	For tubing outside diameter of 1/4"
Ambient temperature	14 °F ... 140 °F
Colour of release ring	grey
Note on materials	RoHS-compliant
Material housing	PBT
Material release ring	POM
Material tubing seal	NBR
Material tubing clamp component	High-alloy stainless steel