

Check that your lighting is in full compliance with standards

- Measures up to 200,000 lux
- I.E.C. spectral correction and incidence correction
- 2000-count display



PHYSICS *Line*

**C.A 811
C.A 813**

Lightmeters

Light

	C.A 811	C.A 813
Measurement range	20 to 20 000 Lux	20 to 200 000 Lux
Accuracy (cell + instrument) Incandescent lamp 2856 K Other light sources	$\pm 3\% + 10$ pt $\pm 18\% + 2$ pt	$\pm 3\% + 10$ pt $\pm 11\% + 2$ pt
Resolution	0.01	
Function	Records maximum value	Displays peak value

- ✓ Hold function
- ✓ Choice of measurement unit Lux / fc
- ✓ Protective shock-proof sheath

Operating conditions:

- Temperature: 0 to +50 °C
- Humidity: <75% RH

Storing conditions:

- Temperature: -20 to +60 °C
- Humidity: <75 % RH

Dimensions: 195 x 60,5 x 38 mm

Mass:

C.A 811 : 214 g,
C.A 813 : 223 g

To order	
C.A 811 Lightmeter	P01. 1724. 01Z
C.A 813 Lightmeter	P01. 1722. 01Z



Electrical,
Mechanical
Maintenance



Museums,
Libraries,
Archives



Distribution



Food Service
Industry