

Northbrook, Illinois • (847) 272-8800  
Melville, New York • (631) 271-6200  
Santa Clara, California • (408) 985-2400  
Research Triangle Park,  
North Carolina • (919) 549-1400  
Camas, Washington • (360) 817-5500



MOELLER GMBH  
MR J LUSCHERT-REINWALD  
HEIN-MOELLER-STRASSE 7-11  
53115 BONN GERMANY

Your most recent Certification is shown below. You may also view this information, or a portion of this information (depending on the product category), on UL's Online Certifications Directory at [www.ul.com/database](http://www.ul.com/database). Please review the text and contact the Conformity Assessment Services staff member who handled your project if revisions are required. For instructions on placing an order for this information in a 3 x 5-inch format, you may refer to the enclosed order form for UL Card Service.

NMMS7 December 5, 2001  
Power Conversion Equipment Certified For Canada

MOELLER GMBH  
HEIN-MOELLER-STRASSE 7-11, 53115 BONN GERMANY

E172143

Accessories, Models DE4-IMO-APP-E, -STD-F; Model DE4-KEY followed by letters or numbers; Models DE4-KEY-2, DF4-NET-DP-F, DV4-320-3K0, -320-4K0, -320-5K5, -320-7K5, DV4-340-3K0, -340-4K0, -340-5K5, -340-7K5, -340-11K.

Brake unit, Cat. No. DE4-BU4-1.

Open-type, 1 or 3 phase, solid-state variable speed AC motor controllers, Models DV4-120-025, -120-037, DV4-322-055, -322-075, -322-1K5, -322-2K2, DV4-340-055, -340-075, -340-1K5, -340-2K2.

Open type power conversion equipment, Models DV5-322-018, -322-037, -322-055, -322-075, -322-1K1, -322-1K5, -322-2K2, DV5-340-037, -340-075, -340-1K5, -340-2K2, -340-3K0, -340-4K0, -340-5K5, -340-7K5.

Power conversion equipment, Models DF-340-037, -340-075, -340-1K5, -340-2K2, -340-3K0, -340-4K0, -340-5K5, -340-7K5, DF5-322-018, -322-037, -322-055, -322-075, -322-1K1, -322-1K5, -322-2K2, DF6-340-11K, -340-15K, -340-18K5, -340-22K, -340-30K, -340-37K, -340-45K, -340-55K, 340-75K, -340-90K, -340-110K, -340-132K, DV6-340-075, -340-1K5, -340-2K2, -340-4K0, -340-5K5, -340-7K5, -340-11K, -340-15K, -340-15K5, -340-22K, -340-30K, -340-37K, -340-45K, -340-55K, -340-75K, -340-90K, -340-110K, -340-132K.

---

LOOK FOR LISTING MARK ON PRODUCT