



Main

Range of product	Merten inserts
Range	Merten
Product or component type	Switch
Device presentation	Mechanism

Complementary

Switch function	1-pole 2-way
Actuator	Rocker
Device mounting	Flush
Fixing mode	By screws and claws
[Ue] rated operational voltage	250 V
Rated current	16 AX
Maximum switching current	10 A
Number of rocker	1
Pilot light	Red indicator
Connections - terminals	Screwless terminals
Material	Metal Plastic

Environment

IP degree of protection	IP20
-------------------------	------

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
Sustainable packaging	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins