



SAGA2 S3S SR Beige

CASUAL

High cut shoe with a trendy look, for work or for the city

Foot protection



Specific benefits



Comfort

- Stabilisation of the foot when walking
- Padded collar for comfort and ankle support



Performance

- Grip on the ground



Easy to use

- Rear lug for easy removal



Hygiene

- Removable insock for easy cleaning

Certifications and norms



EN ISO 20345

S3S HRO WPA FO A E SR

Applications

- Finishing works / Craftsmanship
- Events & scenic
- Law enforcement
- Light industry
- Maintenance
- Temporary work

Protects against risks



Antistatic



Heat



Shock



Slip



SAGA2 S3S SR Beige

CASUAL

Foot protection

High cut shoe with a trendy look, for work or for the city

Standards - Details

Technical details

Shoe type	High shoe
Outsole material	Nitrile rubber, EVA
Anti-perforation insert	Metal free
Upper material	Leather
Upper finition material	Nubuck
Safety toe-cap	Composite
Lining material	Polyester
Footbed material	EVA, Polyester
Footbed characteristic	Removable, Breathable, Pre-molded
Outsole finition	Welded
Weight (g per shoe)	630
Size range	39 → 48



SAGA2 S3S SR

CASUAL

High cut shoe with a trendy look, for work or for the city

Safety footwear

Logistics information

Reference	Colour	Size	Designation	EAN13	Box code			Weight			
SAGA2S3SBE39	Beige	39	SAGA2 S3S SR	3295249291754	13295249291751	5	1	8.02 kg	65.0 cm	28.0 cm	32.5 cm
SAGA2S3SBE40	Beige	40	SAGA2 S3S SR	3295249292881	13295249292888	5	1	11.6 kg	65.0 cm	28.0 cm	32.5 cm
SAGA2S3SBE41	Beige	41	SAGA2 S3S SR	3295249292898	13295249292895	5	1	8.602 kg	29.0 cm	65.2 cm	33.6 cm
SAGA2S3SBE42	Beige	42	SAGA2 S3S SR	3295249292904	13295249292901	5	1	9.05 kg	31.2 cm	64.0 cm	37.0 cm
SAGA2S3SBE43	Beige	43	SAGA2 S3S SR	3295249292911	13295249292918	5	1	9.528 kg	30.8 cm	63.8 cm	37.6 cm
SAGA2S3SBE44	Beige	44	SAGA2 S3S SR	3295249292928	13295249292925	5	1	9.59 kg	30.4 cm	65.0 cm	37.6 cm
SAGA2S3SBE45	Beige	45	SAGA2 S3S SR	3295249292935	13295249292932	5	1	9.686 kg	30.4 cm	64.6 cm	37.4 cm
SAGA2S3SBE46	Beige	46	SAGA2 S3S SR	3295249292942	13295249292949	5	1	10.332 kg	30.8 cm	65.0 cm	37.6 cm
SAGA2S3SBE47	Beige	47	SAGA2 S3S SR	3295249292959	13295249292956	5	1	13.0 kg	65.0 cm	30.0 cm	36.5 cm
SAGA2S3SBE48	Beige	48	SAGA2 S3S SR	3295249292966	13295249292963	5	1	13.2 kg	65.0 cm	30.0 cm	36.5 cm
SAGA2S3SNO39	Black	39	SAGA2 S3S SR	3295249291778	13295249291775	5	1	8.0 kg	31.0 cm	62.4 cm	36.8 cm
SAGA2S3SNO40	Black	40	SAGA2 S3S SR	3295249293062	13295249293069	5	1	8.1 kg	30.4 cm	61.6 cm	37.0 cm
SAGA2S3SNO41	Black	41	SAGA2 S3S SR	3295249293079	13295249293076	5	1	8.3 kg	30.2 cm	62.0 cm	37.2 cm
SAGA2S3SNO42	Black	42	SAGA2 S3S SR	3295249293086	13295249293083	5	1	9.076 kg	30.6 cm	64.4 cm	37.6 cm
SAGA2S3SNO43	Black	43	SAGA2 S3S SR	3295249293093	13295249293090	5	1	9.1 kg	34.0 cm	67.0 cm	39.2 cm
SAGA2S3SNO44	Black	44	SAGA2 S3S SR	3295249293109	13295249293106	5	1	9.3 kg	67.0 cm	33.8 cm	39.0 cm
SAGA2S3SNO45	Black	45	SAGA2 S3S SR	3295249293116	13295249293113	5	1	9.4 kg	33.8 cm	67.2 cm	39.2 cm
SAGA2S3SNO46	Black	46	SAGA2 S3S SR	3295249293123	13295249293120	5	1	9.7 kg	67.2 cm	33.8 cm	39.2 cm
SAGA2S3SNO47	Black	47	SAGA2 S3S SR	3295249293130	13295249293137	5	1	10.2 kg	33.8 cm	67.4 cm	39.2 cm
SAGA2S3SNO48	Black	48	SAGA2 S3S SR	3295249293147	13295249293144	5	1	10.2 kg	34.2 cm	67.2 cm	39.2 cm
SAGA2S3SMA39	Brown	39	SAGA2 S3S SR	3295249291761	13295249291768	5	1	8.01 kg	28.8 cm	64.0 cm	33.0 cm
SAGA2S3SMA40	Brown	40	SAGA2 S3S SR	3295249292973	13295249292970	5	1	8.128 kg	28.2 cm	65.0 cm	33.4 cm
SAGA2S3SMA41	Brown	41	SAGA2 S3S SR	3295249292980	13295249292987	5	1	8.674 kg	28.8 cm	65.2 cm	34.2 cm
SAGA2S3SMA42	Brown	42	SAGA2 S3S SR	3295249292997	13295249292994	5	1	9.344 kg	30.6 cm	64.4 cm	37.2 cm
SAGA2S3SMA43	Brown	43	SAGA2 S3S SR	3295249293000	13295249293007	5	1	9.344 kg	30.8 cm	64.2 cm	37.2 cm



SAGA2 S3S SR

CASUAL

High cut shoe with a trendy look, for work or for the city

Safety footwear

Logistics information

Reference	Colour	Size	Designation	EAN13	Box code			Weight			
SAGA2S3SMA44	Brown	44	SAGA2 S3S SR	3295249293017	13295249293014	5	1	9.648 kg	30.8 cm	64.2 cm	37.6 cm
SAGA2S3SMA45	Brown	45	SAGA2 S3S SR	3295249293024	13295249293021	5	1	12.6 kg	65.0 cm	30.0 cm	36.5 cm
SAGA2S3SMA46	Brown	46	SAGA2 S3S SR	3295249293031	13295249293038	5	1	10.38 kg	30.8 cm	64.0 cm	37.6 cm
SAGA2S3SMA47	Brown	47	SAGA2 S3S SR	3295249293048	13295249293045	5	1	13.0 kg	65.0 cm	30.0 cm	36.5 cm
SAGA2S3SMA48	Brown	48	SAGA2 S3S SR	3295249293055	13295249293052	5	1	13.2 kg	65.0 cm	30.0 cm	36.5 cm



Multiple sales



Minimum sales



Box Width



Box Depth



Box Height