

GGBL6022CS

Lisse - universal dimmer - 2 gangs - 2 way - 250W/VA



Main

Range	Lisse
Product or component type	Dimmer
Device presentation	Complete product
Load type	Incandescent lamp : 250 W 230 V AC halogen lamp :
Colour tint	Matt white
Quantity per set	Set of 1

Complementary

Device mounting	Wall mounted
Dimmer application	Inductive load Resistive load
[Ue] rated operational voltage	230 V AC 50 Hz
Number of gangs	2 gangs
Connections - terminals	Screw terminals
Fixing mode	By screws : M3.5 25 mm
Material	Urea (carbamide) :
Type of packing	Bag
Height	43.6 mm
Width	87 mm
Depth	87 mm
Product weight	0.097 kg

Environment

standards	BS EN 60669-2-1
IP degree of protection	IP20

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.