SCHAEFFLER

Needle roller bearings NA6910-ZW-XL (Series NA69..-ZW)

Dimension series 69, double row

The datasheet is only an overview of dimensions and basic load ratings of the selected product. Please always observe all the guidelines in these overview pages. Further information is given on many products under the menu item "Description". You can also order comprehensive information via the Catalogue ordering system (https://www.schaeffler.de/content.schaeffler.de/en/news_media/index.jsp) or by telephone on +49 (91 32) 82 - 28 97.

d	50	mm	
D	72	mm	
B	40	mm	
F	58	mm	
r_{min}	0,6	mm	
s	0,5	mm	Axial displacement
m	515	g	Mass
C_r	82000	N	Basic dynamic load rating, radial
C_{0r}	139000	N	Basic static load rating, radial
C_{ur}	23800	N	Fatigue limit load, radial

n_G	7800 1/min	Limiting speed
$n_{\vartheta r}$	4200 1/min	Reference speed
		Double row




S