
2101 : Steel Pipe Cutter





Description

Max thickness: 7 mm.
Designed for cutting large diameter pipes, it is fitted with a second handle on the side opposite the feed screw allowing it to be operated by 1 or 2 people. For quickly cutting steel pipes (gas, API, etc.) cleanly and squarely. Removable auxiliary handle attaches to adjusting handle to assist operation. Also works on grey cast iron pipes with special cutting wheels fitted (Ref. 210142).

References

Sku	A pipe "	A pipe mm	L mm	H mm	E maxi mm	kg
210145	2 - 4	60 - 114	1030	235	7	9,000
210165	4 - 6	114 - 165	1110	260	7	10,300

