



CWT2-B

SOLDERSLEEVE WIRE SPLICE BLUE, OD MAX=4.4mm, 1.8-2.5mm² (AWG 18-12)

Product Properties:

Colour	Blue
Operating temperature	-55-125 °C
Voltage max	600V
Connector type	Lödskarvhylsa, dubbelring

Dimensions:

MOQ	50 .
Unit	pcs
Nominal cross section	1.8-2.5 mm ²

Approvals:

Compliance:

Conflict Minerals	Yes, see report under tab "Documents"
Iron and Steel Sanction	Compliance
Link to manufacturer COC	https://www.te.com/commerce/alt/SinglePartSearch.do?PN=493995-000
REACH	Yes. CAS 7439-92-1, 32 %, CAS 7440-43-9, 18 %
RoHS	No
SCIP	5baad761-bcf9-4b10-a101-a5e67076a58f
ECCN (EU)	No CLASS
ECCN (US)	EAR99

Other information:

ETIM-Class	EC000466 - Heat-shrink crimp connection
ETIM-Release	9.0
Trademark	TE Connectivity

Product Group	Soldersleeve wire splices
Search Description	493995-000, B-008-14
Alternative SKU	CWT2-B

Logistic information:

Barcode	733117640019
Country of origin	MX
Item status	Stock item, normally in stock with reservation for in between sales.
MOQ	50 .
Stock code	CWT2-B
Taric code	85369010
Unit	pcs

*We reserve the right to make technical changes and disclaim any typographical errors.