

Features

- Phillips precision screwdriver.
- Blade Ø 3mm.
- Size PH-0 3.0x60mm.
- Total length 164mm +/- 3 mm.
- Rotating cap.
- Ergonomic anti-slip bi-component handle for a safe, light and comfortable grip.
- Chromo-Vanadium-Molybdenum steel blades with black tips having a black oxide treatment.
- Laser marking.
- Made in Italy.

RS PRO Phillips precision screwdriver PH-0

RS Stock No.: (0429676)



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

- *Phillips precision screwdriver.*
 - *Ø Blade: 3mm*
 - *Tip Length: 3mm*
 - *Tip Width: PH-0*
 - *Length of the blade: 60mm*
 - *Rotating cap*
- *Chromo-Vanadium-Molybdenum steel blades with black tips having a black oxide treatment.*
- *Ergonomic anti-slip bi-component handle for a safe, light and comfortable grip.*
- *This precision screwdriver is ideal for different applications in microelectronics, jewellery making, laboratory, watch making and repairs, DIY.*

General Specifications

Tip	Phillips
Ø Blade	3 mm
Tip Length	3 mm
Tip Width	PH-0
Size (mm)	PH-0 3.0x60mm
Length of the blade	60 mm
Total length	164 mm +/-3 mm
Net weight	19.5 g +/-3 mm
Type of material	Chromo-Vanadium-Molybdenum steel blades with black tips having a black oxide treatment
ESD Safe	NO
Handle colour	red/black